

NRC Publications Archive Archives des publications du CNRC

NRC 3D imaging technology for museum and heritage applications

Taylor, J.; Beraldin, J-A; Godin, G.; Cournoyer, L.; Baribeau, R.; Rioux, M.; Domey, J.

This publication could be one of several versions: author's original, accepted manuscript or the publisher's version. / La version de cette publication peut être l'une des suivantes : la version prépublication de l'auteur, la version acceptée du manuscrit ou la version de l'éditeur.

For the publisher's version, please access the DOI link below. / Pour consulter la version de l'éditeur, utilisez le lien DOI ci-dessous.

Publisher's version / Version de l'éditeur:

<https://doi.org/10.1002/vis.311>

The Journal of Visualization and Computer Animation, 14, July 3, pp. 121-138, 2003

NRC Publications Archive Record / Notice des Archives des publications du CNRC :

<https://nrc-publications.canada.ca/eng/view/object/?id=ffa9a743-572f-4018-a91b-0a35f3496e3d>

<https://publications-cnrc.canada.ca/fra/voir/objet/?id=ffa9a743-572f-4018-a91b-0a35f3496e3d>

Access and use of this website and the material on it are subject to the Terms and Conditions set forth at

<https://nrc-publications.canada.ca/eng/copyright>

READ THESE TERMS AND CONDITIONS CAREFULLY BEFORE USING THIS WEBSITE.

L'accès à ce site Web et l'utilisation de son contenu sont assujettis aux conditions présentées dans le site

<https://publications-cnrc.canada.ca/fra/droits>

LISEZ CES CONDITIONS ATTENTIVEMENT AVANT D'UTILISER CE SITE WEB.

Questions? Contact the NRC Publications Archive team at

PublicationsArchive-ArchivesPublications@nrc-cnrc.gc.ca. If you wish to email the authors directly, please see the first page of the publication for their contact information.

Vous avez des questions? Nous pouvons vous aider. Pour communiquer directement avec un auteur, consultez la première page de la revue dans laquelle son article a été publié afin de trouver ses coordonnées. Si vous n'arrivez pas à les repérer, communiquez avec nous à PublicationsArchive-ArchivesPublications@nrc-cnrc.gc.ca.



National Research
Council Canada

Conseil national
de recherches Canada

Institute for
Information Technology

Institut de technologie
de l'information

NRC - CNRC

NRC 3D Technology for Museum and Heritage Applications *

Taylor, J., Beraldin, J.-A., Godin, G., Cournoyer, L., Baribeau, R.,
Blais, F., Rioux, M., and Domey, J.
2003

* published in The Journal of Visualization and Computer Animation.
Volume 14, (3), 2003. pp. 121-138. NRC 46586.

Copyright 2003 by
National Research Council of Canada

Permission is granted to quote short excerpts and to reproduce figures and tables from this report,
provided that the source of such material is fully acknowledged.

Submitted to: The Journal of Visualization and Computer Animation

NRC 3D Imaging Technology for Museum & Heritage Applications

J. Taylor, J-A Beraldin, G. Godin, L. Cournoyer, R. Baribeau, M. Rioux & J. Domey

Visual Information Technology

Institute for Information Technology

National Research Council of Canada

Ottawa, Canada, K1A OR6

Tel. (1) 613 991 1127 Fax. (1) 613 952 0215

email: john.taylor@nrc-cnrc.gc.ca

Abstract

The National Research Council of Canada (NRC) has developed and patented three high-resolution 3D imaging systems and processing algorithms which have been applied to a wide range of museum and heritage recording applications. The systems have been designed for different imaging applications and, in collaboration with a number of national and international museums and cultural agencies, have been used to scan a wide variety of objects and sites. The objective of this paper is to present a summary of the 3D technology and examples of its heritage applications.

Keywords: 3D imaging, museum and heritage applications, laser range sensing, shape and appearance modeling.

Introduction:

The Visual Information Technology Group of the National Research Council of Canada (NRC), has developed three high resolution 3D digital or “laser scanner” imaging systems and processing algorithms which have been applied to a variety of heritage recording projects. These projects have been undertaken in collaboration with several Canadian museums including the Canadian Conservation Institute, the Canadian Museum of Civilization and the National Gallery of Canada. In addition, we have also collaborated on several international demonstration projects with institutions including the British Museum, the Centre de recherche et de restauration des musées de France, the Peabody Museum, the Israel Antiquities Authority, the State Administration of Cultural Heritage in China and in Italy with the Universities of Lecce, Florence, Padova, Ferrara, and Stanford.

One of the systems, the High Resolution Color Laser Scanner, has been used for scanning typical museum and art gallery collections including paintings, ethnographic and archaeological collections and natural history specimens. Two monochrome systems, the Biris 3D Laser Camera and the Large Volume Laser Scanner, have been used in the field to digitize archaeological site features, architectural elements on historic buildings and large sculptures.

The purpose of this paper is to present a summary of the 3D technology and some examples of the museum and heritage recording applications demonstrated to date.

NRC 3D Imaging Systems

The three laser scanner systems use triangulation based scanning and detection systems and are designed for different types of objects and imaging applications.

Autosynchronized Spot Scanning Technology

Two of the systems, the High Resolution Color Laser Scanner and the Large Volume of View Scanner (also known as a Random Access Camera) are based on the patented autosynchronized spot scanning principle [1]. The camera configuration (Figure 1) differs from the usual spot triangulation of other systems in that the directions of projection of the laser beam and the optical axis of the detection system are rotated synchronously through a double-sided mirror. The camera works by projecting a small low power – object safe - laser spot from a laser source to the object via one side of the scanning mirror. The spot is then imaged on a charge-coupled device (CCD) detector via the opposite side of the scanning mirror and the spatial (x,y,z) coordinates of the spot on the object are obtained by triangulation. As such, the instantaneous field of view of the position detector follows the spot as it scans the scene. The focal length of the lens is therefore related only to the desired depth of field or measurement range and not to the total lateral field of view.

The autosynchronized-scanning configuration offers a number of significant features that alleviate compromises between field of view, resolution and shadow effects. It allows very large fields of view, which enables full coverage of the scene without

compromising the measurement uncertainty σ_z . With smaller triangulation angles, a reduction of shadow effects is inherently achieved and, due to the small instantaneous field of view, the system is relatively immune to effects from ambient light. Speckle noise is reduced through spatial filtering by way of the synchronous scan/detection arrangement. It also yields a considerable reduction in the optical head size compared to conventional triangulation methods.

Figure 2 illustrates the resolution limits of the autosynchronized technology in relation to the size of object to be scanned. In the X and Y directions (perpendicular to the laser projection), optical triangulation is limited by the diffraction of the laser beam [2,3,4]. As shown in the diagram, the laser beam does not maintain collimation with distance. The smaller the beam, the larger is the divergence produced by diffraction. The solid line shows the relationship between the X and Y axis and physical dimensions of the object. While diffraction imposes resolution constraints on the X and Y axes, in a well designed system, the Z axis resolution is limited by laser speckle as shown in the dotted line [5].

High Resolution Color Laser Scanner

For scanning museum objects such as paintings, ethnographic and archaeological collections and natural history specimens, one very important feature of the autosynchronized system is that two relatively simple modifications can be made which enable simultaneous shape and color digitization. As illustrated in Figure 3, three laser wavelengths - red, green and blue (RGB) are used as the laser source. When superimposed

in the scanning system, it results in the projection of a 50 – 100 micron diameter “white” laser spot on the object. In the detector, a color separation device such as a prism or a dispersive optical element is added near the lens to split the three RGB wavelengths reflected from the object on the CCD detector. The amplitudes of the three peaks are converted into reflectance values for the three wavelengths by a calibration process that takes into account the geometry of illumination and detection at each surface element [6]. Due to the simultaneous position and amplitude digitizing of the three colors on the CCD, the geometric shape (x,y,z) data and the color (R,G,B) data are recorded in perfect registration. This is a unique feature of the technology – particularly for recording important works of art.

In operation, the camera (Figure 4a) is mounted on a stable three degree-of-freedom translation stage (illustrated in Figure 4b), which is also equipped with a rotation table. Depending on the shape of the object, scans are made either by rotating the object on the rotation table or by scanning successive views using the translation stage. Each view is composed of 1024 profiles and each profile contains 1024 coordinates of x, y, z, R, G, B shape and color data (Figure 4c). In order to digitize a complete object, a series of successive scans or overlapping multiple images are recorded over the complete surface of the object. The scans are subsequently merged (Figure 4d) into a final archival quality 3D digital model of the object (Figure 4e).

In its maximum resolution configuration, this system provides a spatial (x and y) resolution of 50 microns (0.050 mm) and a depth (z) uncertainty of 10 microns (0.010 mm). This resolution is sufficient to record and examine fine brush stroke details on paintings as well as tool mark features on sculptures and archaeological objects. Other specifications of the High Resolution Camera in comparison to the other NRC camera systems are presented in Table 1.

On a commercial basis, NRC has licensed this technology to Arius3D (<http://www.arius3d.com>).

The Large Volume of View (Random Access) Laser Scanner

The Large Volume of View Laser Scanner (Figure 5a) – which is also known as a Random Access Scanner - is also based on NRC's autosynchronized laser scanner technology [7]. It is a dual axis scanning system and is designed for high-resolution monochrome 3D digitization of large structures.

The basic optical configuration for the system depicted in Figure 5b. The *x*-axis scanner achieves the synchronised scanning, while the *y*-axis scanner provides deflection of both the projected and the detected beam. Both mirrors are driven by galvanometers. This configuration enables two imaging modes. For raster mode imaging, the *x*-axis scanner (fast axis) is used for the line scanning while the *y*-axis (slower speed) vertically deflects the scanned beam to produce a raster image. For panoramic scan mode imaging,

the x -axis scanner is used for vertical scans while the camera is rotated on a motorized pan and tilt stage to record panoramic views of the scene. In operation, the scanner can be mounted either on a conventional photographic tripod (Figure 5c) or on a custom designed telescoping tripod, which can be raised to a height of 10 m (Figure 5d).

The system allows 3D recordings at a camera to object distance (camera standoff) which ranges from 50 cm to 10 m. At a standoff of 50 cm, it provides a resolution of 70 microns (0.07 mm), which increases as the square of the distance. For example, at a 10 m standoff, the resolution is 5 mm. Spatial sampling resolution along the x and y scan directions is determined by the laser beam diffraction limit as discussed above. Theoretical predictions and laboratory measurements have shown that images with a resolution of more than $10,000 \times 10,000$ are possible. This spatial resolution combined with a z measurement uncertainty of better than 0.1 mm at close range yield very high-resolution images. Other specifications are listed in Table 1.

For museum and heritage applications, the system has been used to for recording archaeological site features in Israel as well as for digitizing large sculptures at the Canadian Museum of Civilization. Although the Large Volume Laser Scanner is currently a research prototype system in our laboratory and is not commercially available for heritage applications, a commercial space flight version was constructed for a space flight by Neptec (<http://www.neptec.com/>) in 2001 [8].

The Biris 3D Laser Camera

The Biris 3D Laser Camera (Figure 6a) is a portable monochrome 3D imaging system developed to work in difficult environments where reliability, robustness, and ease of maintenance are as important as accuracy [9]. Based on NRC's patented BIRIS dual aperture technology, as illustrated in Figure 6b, the main components of the Biris camera are a standard CCD camera, a camera lens, and a mask with two apertures. This mask replaces the iris of the camera lens - hence the name Bi-iris. A laser line, produced by a solid-state laser diode and a cylindrical lens, is projected on the object. A double image of the laser line is measured on the CCD camera at $p1$ and $p2$. The separation between the two imaged lines and their relative location on the CCD are proportional to the distance between the object and the camera. Hence, they provide information about the shape and dimensions of the object. Furthermore, this technique, when combined with advanced signal processing algorithms, allows Biris to become very tolerant of ambient light illumination, e.g. sunlight. This is particularly important for archaeological and architectural field recording applications.

The camera, controlled by a laptop computer, is mounted either on a conventional tripod (Figure 6c) or on a motorized linear translation stage (Figure 6d). The Biris camera has a maximum range (camera to object distance) of 2 m and an accuracy of 80 microns (0.08 mm) at a range of 0.3 m and 1.8 mm at 1 m. Additional specifications are provided in Table 1.

We have used the Biris system to digitize architectural building elements and sculptures in Italy. In addition, Innovision 3D has also used the scanner to record a section of a Hieroglyphic Stairway at the Peabody Museum and archaeological sites in China.

Commercially, NRC has licensed this technology to the ShapeGrabber Corporation (<http://www.shapegrabber.com/>). Innovision 3D provides a commercial scanning service using this scanner (<http://www.innovision3d.com/>).

Model acquisition and construction

A model is a digital representation of the geometry and appearance of an object on which one can perform operations. Our strategy is to acquire a high-resolution geometric model of the surface, along with parameters of a reflectance model. The model is represented as a triangular mesh at a resolution comparable to the original geometric data, with a colour-per-vertex description of a diffuse reflectance model. This representation, quite generic in nature, embeds all the information gathered by the sensing process. Analytical tasks can then be performed on the model (or in some cases on the original data). This model also fits directly with current polygon-based rendering hardware. Other representations for display purposes can then be derived from the high-resolution mesh. However, the high-resolution mesh can be viewed as the *archival quality* digital record or

3D digital reference model of the object or scene, which serves as the starting point for all subsequent studies and/or transformations.

Constructing the models

In using 3D digitizing for analytical applications, there are several situations where a single image suffices to perform a task, for example detection and monitoring of cracks, or documentation of tool marks on specific areas of a work. However, most objects and environments require the acquisition of more than one range image in order to achieve sufficient coverage of the surface of interest. The necessary number of images will depend on the shape of the object and its amount of self-occlusion, the eventual presence of obstacles to sensor positioning, as well as on the size of the object if it exceeds the field of view of the sensor. Another benefit of merging different views is that the unavoidable noise present in the original data is filtered through the integration process, given that there are no biases in the data.

We have collaborated with researchers at InnovMetric Software Inc. and the Canadian Conservation Institute on the development of 3D modeling methodology for the construction of models from a set of range images [10]. This approach, described in Figure 7, is now commercially implemented in InnovMetric's *PolyworksTM* software suite [11]. The first three steps form the acquisition loop: range images are acquired one at a time, until the desired surface coverage is obtained; a user-guided tool sequentially aligns

(or registers) each new image with the previous ones, and to rapidly detect surface areas not yet measured. The following steps constitute the modeling sequence: these completely automated steps globally refine the alignment between images, integrate them into a unified model that can be directly used, or alternately geometrically compressed and texture-mapped. If required, the models can be manually edited at any step of the modeling sequence.

Appearance modeling

As described above, the High Resolution Color Scanner uses a three-wavelength RGB laser source as the illuminant. The detector sensor measures the energy reflected from the object at each component wavelength. This quantity is a function of the absolute power of the illuminating laser, the distance between the sensor and the surface, the orientation of the imaged surface element relative to the camera, as well as the intrinsic reflectance properties at that point on the surface.

With active range sensing, the position and orientation of the surface can be derived from the range data, and the power of the incident laser is monitored. Since optical triangulation relies on controlling the angles of incidence and measuring the direction of reflected light, the remaining unknown element in the image formation process is the intrinsic reflectance function. Under certain conditions, the parameters of a dichromatic model, composed of the sum of a diffuse and a specular component, can be computed [12].

Often, only the diffuse component will be of interest, since the specular part is more difficult to estimate, and may not be observable at all points on the surface given a finite set of observations. Each view in the set of images provides one pair of incident and reflected directions. Thus, for each sensed surface element, assuming a dichromatic model, at least the diffuse Lambertian component can always be estimated.

Derived representations

Derived graphical representations can be obtained from the high-resolution model. For models that incorporate colour information, perhaps the most useful one for visualization applications is the texture-mapped compressed mesh model. One can compute a texture to be applied on a compressed version of the original model in order to approximate the appearance of the full resolution coloured model (Figure 8). An algorithm for the automatic generation of this map is coupled with the vertex removal mesh compression method [13]. It requires that, during the geometric compression, the algorithm keep track of where each removed vertex projects on the compressed version of the model. When the desired level of compression is reached, the original vertices are projected and transposed into the associated triangle in a tessellated texture map. The main challenge is to tessellate the rectangular texture map efficiently, given a set of triangles of varying proportions and size, while preserving as much of the colour information as possible, and avoiding discontinuities between adjacent model triangles. For virtual display applications, this is a very important aspect for museums. The use of 3D models which represent the

shape, subtle color variations, material characteristics (ivory, bone, stone, metal, wood) and features such as tool mark details as closely as possible to the actual object is a paramount consideration. In short, the *fidelity* of the 3D models to the actual objects is a priority.

Alternately vertices of the high-resolution model can be handled as a cloud of points that is fed into a point-based rendering. Compared with the original points from the simple union of the original images, vertices of the integrated model undergo filtering through the weighted averaging surface reconstruction, and are organized in a more regular sampling pattern on the surface.

Museum and Heritage Applications

During the research and development phase of the technology, we have collaborated on a number of projects to test and demonstrate a number of “real life” museum and heritage recording applications with several Canadian and international museums and cultural agencies. Some projects included testing "museum applications" by scanning objects typically found in museums and art galleries including paintings, small sculpture, archaeological and ethnographic collections as well as natural history specimens. Other projects included demonstrations of the “heritage applications” for recording remote archaeological site features, architectural building elements on historic buildings as well as large sculptures. The scope of the applications covered a wide range of activities from the provision of an archival 3D digital model for future reference in the event of a disaster, to

interactive displays, to conservation and art historical research and for replication. In instances the data augments existing documentation techniques and in others it provides a completely new level of information unobtainable from other techniques [14,15]. Example applications are presented in the following sections.

3D Virtual Museum Display and Exhibition Applications

Three-dimensional models of museum objects that retain close fidelity of the 3D models to the actual objects provide some unique virtual display and exhibition applications for museums. For example, using information kiosks - either in the museum or in a remote site connected to a high-speed communication network – visitors can interactively examine 3D models from any perspective in stereo. The models can also be incorporated into 3D VR Theatre presentations [16] and virtual museum web exhibitions.

This application was demonstrated in two exhibitions in collaboration with the Canadian Museum of Civilization (CMC). The first was *The 3rd Dimension: A New Way of Seeing in Cyberspace* at CMC in 1997 [17]. For exhibition, 3D images of objects from the Museum's collection were digitized using a prototype commercial color laser scanner (Figure 9a). Two interactive display station information kiosks were used for stereo image display – one at the Museum (Figure 9b) and the second “remote site” at the Royal British Columbia Museum in Victoria Canada. Visitors in either museum could select an object from a menu, examine stereoscopic 3D images of it and access associated text information.

Stereo glasses were provided for viewing the images. In addition to rotating the object, visitors could zoom in and examine specific details of interest.

The second was a virtual web exhibition *Inuit 3D* one of six inaugural Virtual Museum of Canada exhibitions launched in April 2001 [18,19]. *Inuit 3D* is an interactive VRML exhibition in which visitors navigate through three exhibition halls in a virtual museum and interactively examine twelve 3D models of objects from the Museum's collection (Figure 10). Introductory QuickTime videos are presented at the entrance to each room to provide information on Inuit history and the Canadian North. Pop-up text panels provide information on the objects as well as on the artists. As discussed above, in preparing the exhibition one of the important factors from the Museum's perspective was the *fidelity* of the 3D models used in the exhibition to the original objects. After reviewing compressed models of varying file sizes, the Museum selected models which had 1000 polygons of shape data with a 512x512 texture map (1.2 KB). While a smaller file size could have been used, it was felt that 1000 polygon models provided a satisfactory level of fidelity to the object – even if it meant longer download times for exhibition visitors.

Remote Recording of Archaeological and Architectural Site Features

We have collaborated with international partners on several projects to demonstrate the applications of the Large Volume of View and Biris systems for remote archaeological and architectural site recording applications as well as to develop a technique to prepare

photo-realistic 3D models of sites by accurate mapping of high-resolution textures recorded by digital photography to 3D models recorded by range cameras.

In 1996, in collaboration with the Israel Antiquities Authority, a pilot project to demonstrate the heritage recording applications of the Large Volume of View Laser Scanner for heritage and conservation professionals was undertaken in Israel. The system was used to scan the Tomb of St. James in Jerusalem, the Holy Sepulchral Lintel in the Rockefeller Museum as well as several archaeological and architectural site features at Caesarea [20].

In 1997, in collaboration with the University of Padova in Italy, the Biris camera was used to digitize the sculpture Madonna col Bambino by Pisano, two bas-reliefs by Donatello as well as deteriorating architectural elements at the Palazzo Della Ragione in Padova. In 1998, in collaboration with the University of Ferrara, it was used to digitize outdoors a number of architectural building elements on the facade of the 8th century Abbey of Pomposa, near Ferrara [21].

In 1999, we collaborated with one of our industrial partners, Innovision 3D, the Canadian Foundation for the Preservation of Chinese Cultural and Historical Treasures and the State Administration of Cultural Heritage (SACH) in China on a pilot project to demonstrate the application of Biris technology for recording archaeological sites in the Three Gorges area of China. As a result of the construction of a hydroelectric dam on the

Yangtze River, an estimated 800-1000 heritage sites along the River will be flooded and lost by 2009. Consequently, the recording of these sites represents a significant challenge for Chinese heritage officials. For the project, a Biris camera was mounted on a linear translation stage and was used to digitize the shape details of rock carvings in a niche at the Bei Shan (Big Foot) rock-carving site near Dazu (Figure 11). The Bei Shan site dates to the ninth century and consists of rock carvings cut into 264 niches on a large hillside rock outcrop. The project led to the donation to SACH of a Biris based ShapeGrabber camera system specifically designed for field recording by InnoVision 3D and the Canadian Foundation.

More recently, we have collaborated with the SIBA Coordination at the University of Lecce in Italy to document, using the latest in multimedia technology, the Crypt of Santa Cristina. The Crypt, located in Carpignano, Apulia was excavated (rupestrian site) around the 9th century c.e. It measures about 16.5 m x 10 m x 2.5 m and has a number of well-preserved frescoes on the walls. During the project we demonstrated a technique that combines high-resolution textures recorded using a digital camera with the shape data recorded from a 3D Laser Scanner to create a complete photo-realistic 3D model of the Byzantine Crypt.

To model the Crypt, a photogrammetric technique was used for the outside (i.e. main and secondary entrances located above the Crypt) and a commercial laser range scanner was used to provide plain clouds of 3D points for the interior of the Crypt itself

(located underground). Texture was acquired with a high-resolution 6 mega-pixel digital camera. The 2D digital photographs were not only used to produce 3D textured models but also to perform geometric measurements. Proper camera calibration and bundle adjustment algorithms combine in digital photogrammetry to give accurate feature coordinates and reliable pose estimations [22].

The 3D modeling of environments or heritage sites like the Crypt is more difficult than object modeling because of the size and complexity involved. Yet, techniques for the creation of accurate and photo-realistic 3D models of sites are important. The 2D photographs that are conventionally used to document and illustrate the site don't show the important aspect of the three-dimensionality of the site. When combined with immersive technologies, a photo-realistic 3D model can be used to prepare a virtual site visit, which is a new and appealing way to study, promote - or even protect - a cultural site (Figure 12). In addition, an accurate 3D site model contains a wealth of information that can be analyzed and enhanced. Features, such as tool marks or surface texture that are small or only visible from a distance can be interactively examined, thus, allowing the study of fine details. To compliment or help plan physical restoration of the site, "virtual restoration" can be applied directly to the digital copy. For example, faded images can be enhanced (Figure 13) and architectural elements that have been added over the years can be removed. To do, so however, it is important to create a geometrically correct visually realistic and highly detailed 3D model [23].

Art Connoisseurship and Conservation Research Applications

Museum curators, art historians and conservators frequently use a variety of traditional scientific techniques such as X-radiography, infrared photography and ultraviolet fluorescence photography for connoisseurship and conservation research examinations on museum collections.

In combination with a variety of computer graphics applications, 3D imaging of works of art offers a significant new analytical tool to curators, historians and conservators, which provides some new and unique types of information which otherwise is not obtainable using traditional techniques. The high-resolution 3D image data contain a wealth of information that can be used for modeling, display, comparison, measurement and analysis applications. For example, curators and historians can zoom in and interactively examine small features such as signatures and tool marks or details on larger objects that can be difficult to study on the actual objects. Art conservators can monitor and measure crack pattern formations on paintings and changes to corrosion formations on sculpture. The following are some examples.

For paintings with varnished surfaces, a unique feature of the shape data captured by the High Resolution Color Scanner is that it originates from the immediate surface of the paint layer, under the varnish, rather than from the varnish surface. This results in a detailed high-resolution recording of the surface relief or 3D structure of the paint layer

from brush stroke details as well as crack pattern formations due to aging. No other technique captures this type of information. As a result, the artificial shading feature as well as contrast enhancement techniques in the graphics package can be used to zoom in and interactively examine features such as the artist's signature (Figure 14), brush stroke details or crack pattern formations.

The graphic applications also provide some unique measurement and monitoring techniques for conservation applications. For example, Figure 15a illustrates the measurement of the length of a canvas tear in a painting while Figure 15b illustrates the measurement of the depth profile of the weathered middle toe on Michelangelo's *David* at the Galleria dell' Accademia in Florence [24].

Another important application is that computer graphics software can be used to generate unique views of objects which can be used for both research and museum display applications. Figure 16 illustrates a flattened or "roll-out" image painted on a Mayan vase prepared for the exhibition *People of the Jaguar* at the Canadian Museum of Civilization. The sequence of images depicting a dancing snake-man tells a story about death and the Underworld around the circumference of the vase. "Rolling-out" the images like this not only facilitates study and comparison with similar images, it can be used for text panels in an exhibition to explain the story as well as in publications [25].

Future Research and Development

To continue development of the technology, there are several areas of research interest to us. We have recently completed a study of the laser scanning of marble – which has unique optical properties [26]. Other areas of ongoing research interests are the development of “cost effective” virtual environment display systems utilizing laptops as well as a content-based 3D search engine for cultural applications [27]. Digital 3D imaging can benefit from advances in VLSI technology in order to accelerate its deployment in many fields like visual communication and industrial automation. NRC and the Institute for Scientific and Technological Research IRST, Trento Italy have initiated activities on VLSI opto-sensors optimized for 3D vision. This project is targeted at the integration of key sensors for 3D vision. These sensors could become an integral part of future intelligent digitizers that will be capable of measuring accurately and simultaneously colour (reflectance) and 3D. This, in turn, will accelerate the development of hand-held 3D cameras, and, multi-resolution random access laser scanners for fast search and tracking of 3D features. All these digitizers will require a thorough VLSI integration of basic laser camera functions to achieve size and cost reduction and most importantly, higher performance. A number of prototype sensors have been fabricated using standard CMOS technology that allows the monolithic integration of photo-sensors, together with readout circuits, and digital signal processors [28].

One area of future research of interest to us is the use of more than three wavelengths for improved color recording using the High Resolution Color camera. As

noted above the current system uses three RGB wavelengths. Recent studies have shown that the average ΔE_{94} accuracy with the actual set of three wavelengths is found to be in the range 3~5 units. This can be reduced to a range of 2~3 units using optimal three wavelengths [29]. A substantial reduction of error is predicted when more than three sampling wavelengths are used, as the average error is found to diminish by 50% each time the number of sampling wavelengths increases by one. The average color error can be brought down to less than one just noticeable difference equivalent with four or five sampling wavelengths [30]. As a result, one area of research we are intending to pursue is the use of five wavelengths to improve the color recording characteristics of the system.

Conclusions

This paper has presented an overview of the imaging systems developed at NRC and some of the museums and heritage recording applications. For heritage recording, perhaps the most important aspect is that the image data obtained using the 3D imaging systems provides an accurate high resolution three-dimensional digital record of the object. This "3D digital model" data can be retained as an archival quality record of the object and used for a variety of activities including display, research, conservation, replication and VR applications.

References

1. Rioux, M., Digital 3-D imaging: theory and applications. *SPIE Proceedings, Videometrics III*, Boston, MA. October 31-November 4, Vol. 2350, 1994. pp. 2-15.
2. Rioux, M., Bechthold, G., Taylor, D., and Duggan, M. Design of a large depth of view three-dimensional camera for robot vision. *Opt. Eng.* 26(12): 1245-1250; 1987. NRC 29130.
3. Rioux, M. Color 3-D electronic imaging of the surface of the human body. *SPIE Proceedings, Automatic Systems for the Identification and Inspection of Humans*, San Diego, CA. July 28-29, 1994. Vol. 2277. pp. 42-54. NRC 38344.
4. Beraldin, J.-A., Blais, F., Cournoyer, L., Godin, G., and Rioux, M. Active 3D sensing. *Modelli E Metodi per lo studio e la conservazione dell'architettura storica*, University: Scuola Normale Superiore, Pisa 10: 22-46; 2000. NRC 44159
5. Baribeau, R., and Rioux, M. Centroid fluctuations of speckled targets. *Appl. Opt.* 30(26): 3752-3755; 1991. NRC 33147 9/10/91.

6. Baribeau, R., Cournoyer, L., Godin, G. and Rioux, M. "Colour Three-Dimensional Modelling of Museum Objects", *Imaging the Past, Electronic Imaging and Computer Graphics in Museum and Archaeology*, British Museum, Occasional Paper Number 114, 1996, London, 199 - 209.
7. Rioux, M., Beraldin, J.-A., Blais, F., Godin, G. and Cournoyer, L., "High Resolution Digital 3-D Imaging of Large Structures", *Three-Dimensional Image Capture, SPIE Proceedings*, Volume 3023, 11 February, 1997, San Jose, CA, 109 - 118.
8. Blais, F., Beraldin, J.-A., Cournoyer, L., El-Hakim, S.F., Picard, M., Domey, J., Rioux, M., The NRC 3D Laser Tracking System: IIT's Contribution to International Space Station Project, *Proceedings of the 2001 Workshop of Italy-Canada on 3D Digital Imaging and Modeling Application of: Heritage, Industry, Medicine, & Land*, Padova, Italy. April 3-4, 2001. NRC 44181.
9. Beraldin, J.-A., Blais, F., Cournoyer, L., Rioux, M., Bernier, F., and Harrison, N., "Portable Digital 3-D Imaging System for Remote Sites", *3D Data Modelling and Imaging, The 1998 IEEE International Symp. On Circuit and Systems*, Monterey, CA, USA: 326-333. May 31-June 3, 1998.
10. Soucy, M., Godin, G., Baribeau, R., Blais, F. and Rioux, M. "Sensors and Algorithms for the Construction of Digital 3-D Colour Models of Real Objects", *ICIP-96*

Proceedings, 1996 IEEE International Conference on Image Processing, Vol. II of III, Lausanne, Switzerland, 16-19 September, 1996, 409-412.

11. Innovmetric Software Inc. Retrieved February 15, 2003 from <http://www.innovmetric.com>
12. Baribeau, R., Rioux M. and Godin G., "Color Reflectance Modelling Using a Polychromatic Laser Range Sensor". *IEEE Trans. Pattern Anal. Machine Int.*, 14(2): (1992), 263-269.
13. Soucy, M., Godin, G., Rioux, M. "A texture-mapping approach for the compression of colored 3D triangulations", *The Visual Computer*, vol. 12, 1996. pp. 503-514.
14. Godin, G., Cournoyer, L., Domey, J. and Taylor, J., "Three-dimensional recording of objects and sites using laser range imaging", *Quaderni 10, Centro di Ricerche Informatiche per i Beni Culturali*, X 2000, ISSN 1126-6090, 139 - 150.
15. Godin, G., Beraldin, J.-A., Taylor, J, Cournoyer, L., Rioux, M., El-Hakim, S., Baribeau, R., Blais, F., Boulanger, P., Picard, M., and Domey, J. , "Active Optical 3-D Imaging for Heritage Applications." *Proceedings of the IEEE Computer Graphics & Applications: Special Issue on Computer Graphics in Art History & Archaeology*,

ISSN 0272-1716, September/October 2002, Vol. 22, No. 5, pp. 24-36. NRC 44945.

16. MacDonald, G., Corcoran, F., Taylor, J., Boulanger, P. and Rioux, M., "CMC's 3D Virtual Reality Theatre: VR Tours of Two Tombs during the Mysteries of Egypt Exhibition", *MMM 99, Modeling Multimedia and Information Systems*, Ottawa, Canada, 4-6 October 1999, (ISBN 981-02-4146-1), pp 167- 177.
17. Livingstone, F., Evans, K., Taylor, J., Rioux, M., and Arsenault-Desfossés, H., "The 3rd Dimension: A New Way of Seeing in Cyberspace", *Electronic Imaging and the Visual Arts, EVA '97 Paris*, Musée du Louvre, Conference Proceedings, 2 Septembre, 1997, 10.1 - 10.13.
18. Corcoran, F., Demaine, J., Picard, M., Dicaire, L-G. and Taylor. J., INUIT 3D: An Interactive Virtual 3D Web Exhibition, *Museums and the Web 2002*, 17-20 April 2002, Boston. Retrieved 15 February 18, 2003 from:
<http://www.archimuse.com/mw2002/papers/corcoran/corcoran.html>
19. Virtual Museum of Canada: Retrieved 15 February 18, 2003 from:
<http://www.virtualmuseum.ca/>
20. Domey, J., Cournoyer, L., Taylor, J. and Letellier, R., Demonstration of Heritage 3-D Imaging Applications in Israel.

Retrieved 15 February 18, 2003 from: <http://www.vit.iit.nrc.ca/Israel/Israel.html>

21. Beraldin, J.-A., Blais, F., Cournoyer, L., Rioux, M., and El-Hakim, S., "Portable Digital 3-D Imaging System for Remote Sites", *Applications of BIRIS Technology to Heritage Applications in Italy 1997-98*. Retrieved 15 February 18, 2003 from:
http://www.vit.iit.nrc.ca/Biris_Italy/3dima.htm
22. Beraldin, J.-A. , Picard, M., El-Hakim, S.F., Godin, G., Valzano, V., Bandiera, A., and Lataouche, D. "Virtualizing a Byzantine Crypt by Combining High-Resolution Textures with Laser Scanner 3D Data." *Proceedings of VSMM 2002*, 25-27 September 2002, Gyeongju, Korea. NRC 44959.
23. Beraldin, J.-A., Picard M., El-Hakim, S.F., Godin, G., Latouche C., Valzano V., Bandiera A., "Exploring a Bysantine Crypt through a High-Resolution Texture Mapped 3D Model: Combining Range Data and Photogrammetry:", *International Workshop on Scanning for Cultural Heritage Recording - Complementing or Replacing Photogrammetry*, Corfu, Greece, Sept. 01 and 02, 2002: NRC 44916
24. NRC 3D Laser Scanning, Participation in the Digital Michelangelo Project, Florence, Italy, February 1999. Retrieved 15 February 18, 2003 from:

http://www.vit.iit.nrc.ca/Florence_99/NRC_3D_Florence.html

25. Ruddell, N., "Mystery of the Maya", *Canadian Museum of Civilization*, 1995, ISBN 0-660-14040-3.
26. Godin, G., Rioux, M., Beraldin, J.-A., Levoy, M., Cournoyer, L. and Blais, F., An assessment of laser range measurement on marble surfaces, à paraître: *5th Conference on Optical 3D Measurement Techniques*, 1-4 octobre 2001, Vienne, Autriche., NRC 44210
27. Paquet, E., Peters, S., Beraldin, J.A., Valzano, V., Vandiera, A. and Banderia, A., "Virtualization, Virtual Environments and Content-Based Retrieval of Three-Dimensional Information for Cultural Applications", *Videometrics VII, Proceedings of Electronic Imaging Science and Technology, SPIE Vol. 5013*, 2003, pp 137-147. NRC 44978.
28. Gonzo, L., Simoni, A., Gottardi, M., Stoppa D. and, Beraldin, J.-A., "Sensors Optimized for 3D Digitization", *IEEE Trans. Intrusm. And Meas.* In press 2003
29. Baribeau, R., Spectral Estimation from Laser Scanner Data for Accurate Color Rendering of Objects, *SPIE 4421*, 2001.

30. R. Baribeau. Optimized spectral estimation methods for improved colorimetry with laser scanning systems. *Proc. 1st Int. Symp. 3D Data Processing, Visualization and Transmission*, Padova (Italy) 2002, Proceedings of IEEE Computer Society, ISBN 0-7695-1521-5, pp. 400-404 (2002).

Table 1**Range Camera Specifications**

Specifications	Color scanner	Large volume- of-view	Biris model M-1
Field of view (deg)	40	40 X 50 or 40 X 200	30 X 200
Minimum range (m)	0.4	0.5	0.3
Maximum range (m)	0.6	10	2.0
Transverse resolution along scanning direction (X–Y)(pixels)	up to 10,000	up to 10,000	up to 1024
Z uncertainty (1σ)	0.01 mm at 0.55 m	0.1 mm at 0.5 m 0.5 mm at 1.5 m 5.0 mm at 10 m	0.15 mm at 0.3 m 1.8 mm at 1.0 m
Data rate (3D points/s)	6250 (3D +RGB)	10,000	15,360
Time for 256 X 256 3D coordinates and RGB image for color scanner (s)	10.5	6.56	4.27
Dimensions (mm)	250 X 200 X 80	200 X 150 X 80	150 X 120 X 60
Weight (kg)	5	4	0.9




Figure 1: The autosynchronized scanning configuration. Similar to photography, the CCD detector is mounted on an angle to conform to the Scheimpflug condition to maximize depth of view.




Figure 2: Physical limits of 3D optical measurements based on laser projection. The solid line shows the relationship between the X and Y axes (direction perpendicular to the laser projection) and the physical dimensions of the object to be scanned; the dotted line is the uncertainty in Z imposed by laser speckle.





Figure 3: For simultaneous color and shape recording using the High Resolution Color Camera, a polychromatic RGB laser source is used to project a “white” laser spot on the object. The triangulated light reflected from the object is separated into its three primary R,G and B wavelengths using a prism for recording by the CCD detector. This results in the simultaneous recording of the shape (x,y,z) coordinates and the color (R,G,B) data in perfect registration.




a



b



c




d




e

Figure 4: (a) The High Resolution Color Camera shown scanning a figurine mounted on the rotation table. (b) Illustration of the three degree-of-freedom translation stage. (c) Front view of the figurine during scanning. The white line is a time exposure of the white laser spot during scanning of a profile. (d) Four images aligned with a different color associated with each image. (e) Side view of the final 3D digital model of the object.



a

b




c

d

Figure 5: (a) The Large Volume Laser Scanner mounted on pan and tilt unit. The system includes a video camera to facilitate remote positioning of the scanner. (b) Schematic optical configuration of the dual axis scanner. (c) The scanner is mounted on a conventional tripod to scan archaeological site features at Caesarea in Israel. (d) The camera is mounted on a telescoping tripod to scan the sculpture Mythic Messengers at the Canadian Museum of Civilization. The sculpture is mounted 4 m above ground on an exterior wall and measures 9 m long x 1.2 m



a



b



c



d

Figure 6: (a) The Biris 3D Laser Camera is a compact and portable monochrome imaging system and is ideally suited for field recording applications. (b) Illustration of the optical principle (c) The camera is shown attached to a motorized rotation stage mounted on tripod. The cases for carrying the system and laptop computer controller are in the foreground. (d) The camera mounted on a linear translation stage imaging a section of a Hieroglyphic Stairway at the Peabody Museum (photo courtesy Innovision 3D Inc.)





Figure 7: From multiple range images to shape and color models.



a1

b1

c1



a2

b2

c2

Figure 8: The high-resolution model of a Haida mask from the Canadian Museum of Civilization (VII-B-136a) is illustrated in (a2) and contains 600,000 polygons of shape information (a1) in a 16.5 MB file. This model is the archival quality model used for research applications and to prepare lower resolution models for other applications. Images (b1) and (b2) illustrate a 10,000 polygon model (b1) with a 1000 x 1000 texture map (b2) in a 6 MB file. This model is suitable for interactive display in a museum kiosk. Images (c1) and (c2) illustrate a 1,000 polygon model (c1) with a 512 x 512 texture map (c2) in a 0.17 MB file. This model is suitable for interactive web display. When the texture

maps are applied to the compressed models, it generates a 3D appearance that approximates the appearance of the full resolution colored model. Thus a close approximation to the fidelity of the high-resolution model is retained in the 3D model used for museum visualization as well as web applications.




a

b

Figure 9: The digitizing system (a) at the Canadian Museum of Civilization scanning an object from the Museum's collection during the exhibition *The 3rd Dimension: A New Way of Seeing in Cyberspace*. Stereo images were displayed in an interactive display station (b) at the Museum and at Royal British Columbia Museum in Victoria.




a



b

Figure 10: (a) View of the Inuit Art Hall in the virtual exhibition *Inuit 3D* from the entrance. “Billboard” images of the objects were placed in individual display cases and images of arctic photographs and prints were added to the walls. Clicking on an object in a display case opens two new pop-up windows (b). The left pop-up window contains the 3D VRML model of the object, which can be interactively examined. The right pop-up window contains information on the object as well as links to related information on other sites.



a

b

c

Figure 11: The Biris system set up on scaffolding at niche #147 at Bei Shan (a and b). At a stand off distance of 0.3 m, the range accuracy is 80 microns. The 3D digital model recorded by the system is shown c. It represents an archival recording of the shape of the carvings in the niche, which can be used to document the condition of the site, to monitor ongoing erosion for conservation applications and to prepare a replica.



a

b


Figure 12: Accurate photo-realistic 3D models of heritage sites offer important new ways to study, promote and protect sites. The portion of the Crypt shown with synthetic shading in (a) illustrates irregular shape of the walls. Capturing the three-dimensionality such as this is an important aspect. (b) Illustrates same portion after texture mapping showing a higher level of realism. (For more information, see Reference 22.)



a

b

Figure 13: Example of a simple virtual restoration, (a) current state of some of the writings, (b) enhanced version with some modifications to the texture image that is re-mapped by simply reloading the 3D model in the viewer. (From Reference 22.)



a

b

Figure 14: (a) Detail of a shaded monochrome range image of the signature area on a Corot painting with artificial shading directed from top. Note the surface relief of the signature from the brush stroke as well as brush stroke patterns. (b) Detail of a monogram and date (RHL:1629) on a wooden panel painting attributed to Rembrandt. As shown by the dark image (top), the monogram and date are barely visible to the eye on the painting. The monochrome range image (bottom) shows details of the monogram and date plus the tree ring structure of the wooden panel. The monogram and date are clearly visible in the center image, which has been produced using color contrast enhancement techniques. These features offer new techniques to curators and art historians for studying artist's signature as well as their unique brush stroke details. The lower plot shows the surface relief from the tree ring structure and can be used for dendrochronology studies.




Figure 15: In addition to display features, measurement and comparison features are an important graphics application of the software for art conservation applications. For example, in (a) the length of the canvas tear between the black dots in a section of a painting measures 31.47 mm. (b) illustrates the measurement of the depth profile of the weathered middle toe (black line) on Michelangelo's *David* at the Galleria dell' Academia in Florence. Measurements such as these can be repeated at different points of time to monitor ongoing changes to features on works of art such as crack formations, changes to corrosion patterns as well as expansion and contraction due to temperature and humidity changes.



a



b

Figure 16: The software can also be used to produce flattened or "roll-out" photographs of images such as rituals, myths, geometric motifs, and hieroglyphs painted on vases for study. Image (a) shows the High Resolution Color Scanner digitizing a cylindrical scan on a Mayan vase. The flattened or "roll-out" image of the painting on the vase is shown in (b). This feature was used to prepare images of a suite of vases for the exhibition *People of the Jaguar* at the Canadian Museum of Civilization as well as for the publication *Mystery of the Maya*.