

NRC Publications Archive Archives des publications du CNRC

Relative significance of NO_x and HCN in fire gas toxicity Tsuchiya, Y.

This publication could be one of several versions: author's original, accepted manuscript or the publisher's version. /
La version de cette publication peut être l'une des suivantes : la version prépublication de l'auteur, la version
acceptée du manuscrit ou la version de l'éditeur.

For the publisher's version, please access the DOI link below. / Pour consulter la version de l'éditeur, utilisez le lien
DOI ci-dessous.

Publisher's version / Version de l'éditeur:

<https://doi.org/10.4224/40001429>

*Paper (National Research Council of Canada. Institute for Research in
Construction), 1989*

NRC Publications Archive Record / Notice des Archives des publications du CNRC :

<https://nrc-publications.canada.ca/eng/view/object/?id=bf7f41c7-30b5-4977-9e5b-25b447b91c25>

<https://publications-cnrc.canada.ca/fra/voir/objet/?id=bf7f41c7-30b5-4977-9e5b-25b447b91c25>

Access and use of this website and the material on it are subject to the Terms and Conditions set forth at

<https://nrc-publications.canada.ca/eng/copyright>

READ THESE TERMS AND CONDITIONS CAREFULLY BEFORE USING THIS WEBSITE.

L'accès à ce site Web et l'utilisation de son contenu sont assujettis aux conditions présentées dans le site

<https://publications-cnrc.canada.ca/fra/droits>

LISEZ CES CONDITIONS ATTENTIVEMENT AVANT D'UTILISER CE SITE WEB.

Questions? Contact the NRC Publications Archive team at

PublicationsArchive-ArchivesPublications@nrc-cnrc.gc.ca. If you wish to email the authors directly, please see the
first page of the publication for their contact information.

Vous avez des questions? Nous pouvons vous aider. Pour communiquer directement avec un auteur, consultez la
première page de la revue dans laquelle son article a été publié afin de trouver ses coordonnées. Si vous n'arrivez
pas à les repérer, communiquez avec nous à PublicationsArchive-ArchivesPublications@nrc-cnrc.gc.ca.

f Ser
11
21d
p. 1643
RC

National Research
Council Canada

Conseil national
de recherches Canada

Institute for
Research in
Construction

Institut de
recherche en
construction

Relative Significance of No_x And HCN in Fire Gas Toxicity

by Y. Tsuchiya

Reprinted from
Fire Safety Science
Proceedings of the Second International Symposium
Tokyo, Japan, June 13-17, 1988
p. 381-390
(IRC Paper No. 1643)

NRCC 31388

IRC LIBRARY M-20

OCT 30 2006

BIBLIOTHÈQUE IRC M-20

Canada

CISTI / ICIST



3 1809 00410 7378

Résumé

Des données d'analyse sur les NO_x dans les produits de pyrolyse/combustion de divers matériaux sont disponibles depuis un certain temps. Cette étude analyse la production des NO_x à partir de données tirées des publications et des expériences de l'auteur. Dans ces expériences, un tissu de polyacrylonitrile a été brûlé dans : a) un tube de quartz, b) un appareil de mesure de l'indice d'oxygène de l'ASTM, c) un appareil calorimétrique de l'ASTM (ou de l'Ohio State University) et d) une chambre pleine grandeur de l'ASTM. La toxicité des NO_x était comparable ou inférieure à celle du HCN. Comme les concentrations de NO_x produits sont nor
dev contribution des NO_x
on.

Relative Significance of NO_x and HCN in Fire Gas Toxicity

YOSHIO TSUCHIYA

Institute for Research in Construction

National Research Council of Canada

Ottawa, K1A 0R6, Canada

ABSTRACT

Analytical data on NO_x in the pyrolysis/combustion products of various materials have been available for some time. In this study, its generation is discussed, based on data obtained from the literature and the author's experiments. In these experiments, polyacrylonitrile fabric was burnt in: (a) a quartz tube, (b) an ASTM oxygen index test apparatus, (c) an ASTM (or Ohio State University) heat release rate apparatus, and (d) an ASTM full-scale room. The toxicity of NO_x was comparable to or less than that of HCN. Since concentrations of NO_x produced are normally much lower than those of HCN, NO_x would be expected to be of minor in fire gas toxicity considerations.

INTRODUCTION

Oxides of nitrogen (NO_x) include, NO , NO_2 , N_2O_3 , N_2O_4 or $(\text{NO}_2)_2$ and N_2O_5 . NO and NO_2 are the most common among them, and therefore only these two will be discussed in this paper.

NO_x may be produced in two ways: by the oxidation of atmospheric N_2 at high temperatures (thermal NO_x), or by the pyrolysis and combustion of nitrogen-containing fuels (fuel NO_x). The generation of thermal NO_x in furnaces or internal combustion engines is of interest mainly in pollution control. In fire gases the thermal NO_x plays an unimportant part, because its formation in diffusion flames is insignificant (1). In this study the significance of fuel NO_x in fire gas toxicity will be discussed, based on analytical data obtained from the literature and in the author's laboratory. Special attention is paid to the relative importance of NO_x and HCN, both of which may be produced from the combustion of nitrogen-containing fuels.

Analytical data on NO_x generation

Some analytical data on NO_x produced in fire or in the pyrolysis/combustion of organic fuels, as reported in the literature, are listed in Table 1 (2-17). Most of them are presented either as quantities produced from a known weight of a fuel, or as gas phase concentrations. Direct comparison of these two kinds of data is difficult, since information necessary for converting from one to the other is often lacking. A high concentration of NO_x , 100 ppm or more, was found only in full-scale room experiments (No.

B2107794

TABLE 1 GENERATION OF NOX IN FIRE EXPERIMENTS

NO. MATERIALS	ATMOSPHERE (A)	TEMP. (B)	NOX (C)	NOX/HCN (D)	GENERATION	NOX ANALYSIS	AUTHOR	YEAR	REF																																																																																																																																																																																																					
1 CELLULAR ACRYLONITRILE			15.6		IN A GLASS BULB	HARGER & HULPIEU METHOD	WATSON	(1951)	2																																																																																																																																																																																																					
2 CELLULAR PVC			8.8							3 ABS			30PPM		NBS SMOKE CHAMBER	COLORIMETRIC TUBES	GROSS	(1968)	3	4 WOOL RUG			25PPM		5 NYLON TYPE RESIN			50PPM		6 COTTON			8PPM		7 AROMATIC POLYAMIDE RUG			18PPM		8 POLYETHER URETHANE FOAM			12PPM		9 UREA-FORMALDEHYDE		500	5PPM	0.005	1G UNDER FLOW	COLORIMETRIC TUBES	BOTT	(1969)	4	10 UREA-FORMALDEHYDE	N2	500	2PPM	11 POLYACRYLONITRILE	N2	500	20PPM	12 POLYACRYLONITRILE		500	25PPM	13 ACRYLIC FIBRE		600	15	(E)	8 TO 60MG IN A TUBE	COLORIMETRIC TUBES	SKIDMORE	(1974)	5	14 ACRYLIC FIBRE		800	11	0.04	15 ACRYLIC FIBRE		1000	18		16 NYLON		600	10		17 NYLON		800	2.2	0.04	18 NYLON		1000	8.8		19 WOOL		600	2.4		20 WOOL		800	1.6	0.02	21 WOOL		1000	6.0		22 POLYURETHAN FOAM		600	4.6		23 POLYURETHAN FOAM		800	3.1	0.07	24 POLYURETHAN FOAM		1000	4.7		25 COMMERCIAL PRODUCTS			87PPM		FULL SCALE ROOM FIRE		ARMSTRONG	(1974)	6	26 TYPICAL ROOM			150PPM	0.2	FULL SCALE ROOM FIRE	ELECTROCHEMICAL & NOIR	HILLENBRAND	(1974)	7	27 IMPROVED ROOM			100PPM	0.9	28 SPACE-AGE ROOM			15PPM	6.5	29 SYNTHETIC POLYMER F.R.			168PPM		10G WITH TORCH IN A BOX		MONTGOMERY	(1975)	8	30 NATURAL POLYMER			126PPM		31 WOOL			10PPM		E-84 TUNNEL	COLORIMETRIC TUBES	PRYOR	(1975)	9	32 RED OAK			10PPM		33 ACRYLIC CARPET			1PPM		34 RIGID PU FOAM	PREHEAT 60		18PPM	0.6	NBS SMOKE CHAMBER	COLORIMETRIC TUBES	LEE	(1975)	10
3 ABS			30PPM		NBS SMOKE CHAMBER	COLORIMETRIC TUBES	GROSS	(1968)	3																																																																																																																																																																																																					
4 WOOL RUG			25PPM																																																																																																																																																																																																											
5 NYLON TYPE RESIN			50PPM																																																																																																																																																																																																											
6 COTTON			8PPM																																																																																																																																																																																																											
7 AROMATIC POLYAMIDE RUG			18PPM																																																																																																																																																																																																											
8 POLYETHER URETHANE FOAM			12PPM																																																																																																																																																																																																											
9 UREA-FORMALDEHYDE		500	5PPM	0.005						1G UNDER FLOW	COLORIMETRIC TUBES	BOTT	(1969)	4																																																																																																																																																																																																
10 UREA-FORMALDEHYDE	N2	500	2PPM																																																																																																																																																																																																											
11 POLYACRYLONITRILE	N2	500	20PPM																																																																																																																																																																																																											
12 POLYACRYLONITRILE		500	25PPM																																																																																																																																																																																																											
13 ACRYLIC FIBRE		600	15	(E)	8 TO 60MG IN A TUBE	COLORIMETRIC TUBES	SKIDMORE	(1974)	5																																																																																																																																																																																																					
14 ACRYLIC FIBRE		800	11	0.04																																																																																																																																																																																																										
15 ACRYLIC FIBRE		1000	18																																																																																																																																																																																																											
16 NYLON		600	10																																																																																																																																																																																																											
17 NYLON		800	2.2	0.04																																																																																																																																																																																																										
18 NYLON		1000	8.8																																																																																																																																																																																																											
19 WOOL		600	2.4																																																																																																																																																																																																											
20 WOOL		800	1.6	0.02																																																																																																																																																																																																										
21 WOOL		1000	6.0																																																																																																																																																																																																											
22 POLYURETHAN FOAM		600	4.6																																																																																																																																																																																																											
23 POLYURETHAN FOAM		800	3.1	0.07																																																																																																																																																																																																										
24 POLYURETHAN FOAM		1000	4.7																																																																																																																																																																																																											
25 COMMERCIAL PRODUCTS			87PPM							FULL SCALE ROOM FIRE		ARMSTRONG	(1974)	6																																																																																																																																																																																																
26 TYPICAL ROOM			150PPM	0.2						FULL SCALE ROOM FIRE	ELECTROCHEMICAL & NOIR	HILLENBRAND	(1974)	7																																																																																																																																																																																																
27 IMPROVED ROOM			100PPM	0.9																																																																																																																																																																																																										
28 SPACE-AGE ROOM			15PPM	6.5																																																																																																																																																																																																										
29 SYNTHETIC POLYMER F.R.			168PPM							10G WITH TORCH IN A BOX		MONTGOMERY	(1975)	8																																																																																																																																																																																																
30 NATURAL POLYMER			126PPM																																																																																																																																																																																																											
31 WOOL			10PPM							E-84 TUNNEL	COLORIMETRIC TUBES	PRYOR	(1975)	9																																																																																																																																																																																																
32 RED OAK			10PPM																																																																																																																																																																																																											
33 ACRYLIC CARPET			1PPM																																																																																																																																																																																																											
34 RIGID PU FOAM	PREHEAT 60		18PPM	0.6						NBS SMOKE CHAMBER	COLORIMETRIC TUBES	LEE	(1975)	10																																																																																																																																																																																																
35 RIGID PU FOAM	PREHEAT135		30PPM	1.7																																																																																																																																																																																																										

TABLE 1 CONTINUED

NO. MATERIALS	ATMOSPHERE TEMP.	NOX	NOX/HCN	GENERATION	NOX ANALYSIS	AUTHOR	YEAR	REF
36 WOOL	800	5N%		MOVING SAMPLE BED	CHEMILUMINESCENCE	MUKAI	(1977)	11
37 DOUGLAS FIR		0.1PPM		3.5G UNDER FLAT HEATER	SALTZMAN COLORIMETRY	HARTUNG	(1977)	12
38 POLYURETHANE		2PPM						
39 FIR PLYWOOD	COMB.475	10PPM		2 TO 12G IN POTTS' POT	CHEMILUMINESCENCE & COLORIMETRIC TUBES	POTTS	(1977)	13
40 RED DAK	COMB.480	10PPM						
41 POLYSTYRENE HIGH IMPACT	COMB.475	4.5PPM						
42 STYROFOAM	COMB.550	15PPM						
43 RIGID POLYURETHANE	COMB.560	95PPM						
44 RIGID POLYURETHANE	PYRD.560	<1PPM						
45 PVF/PHENOLIC PANEL	600	0.37	0.04	0.25G IN A TUBE	GRIESS-SALTZMAN METHOD	SPURGEON	(1977)	14
46 FR URETHANE FOAM	600	0.02	0.002					
47 AROMATIC POLYAMIDE	600	0.53	0.04					
48 FR WOOL	600	0						
49 PVF/PHENOLIC PANEL		0.01	0.02	NBS SMOKE CHAMBER				
50 AROMATIC POLYAMIDE		0.26	0.1					
51 FR WOOL		0.45	0.03					
52 COTTON BATTING	1.0M/CM2	10PPM(F)	2.7	OSU HRR IN 10 MINUTES	CHEMILUMINESCENCE	HERRINGTON	(1978)	15
53 ISOCYANURATE FOAM	1.0M/CM2	24PPM	1.5			(AND 1979)		
54 RIGID PU FOAM	1.0M/CM2	61PPM	1.8					
55 RESILIENT PU FOAM	1.0M/CM2	122PPM	4.9					
56 WOOL FABRIC		2.7(G)	0.09	BY A TRAVERSING FLAME	NO3 ELECTRODE & CHEMILUMINESCENCE	HOSCHKE	(1981)	16
57 NOMEK FABRIC		6.0	1.1					
58 MODACRYL DRAPE		6.2	0.09					
59 FR PU FOAM		1.7	0.3					
60 WOOL FABRIC		9.3	26					
61 NOMEK FABRIC		28	2.2					
62 MODACRYL DRAPE		15	0.9					
63 FR PU FOAM		17	2.4					
64 HOUSEHOLD GOODS	870	90PPM	0.36	FULL SCALE ROOM FIRE	COLORIMETRY(H)	MORIKAWA	(1985)	17
	700	170PPM	3.7					

(A) ATMOSPHERE IS AIR UNLESS OTHERWISE SPECIFIED

(B) NOMINAL TEMPERATURE IN CENTIGRADE

(C) NO2/SPECIMEN IN MG/G UNLESS OTHERWISE SPECIFIED

(D) MOLE RATIO

(E) AVERAGE VALUES FOR THE MATERIAL

(F) ORIGINAL DATA WERE PRESENTED IN MG/MIN.M2

(G) ORIGINAL DATA WERE PRESENTED IN G/M2

(H) NAPHTHYL ETHYLENEDIAMINE

26, 27, 64 in the Table), in an Ohio State University heat release rate apparatus (No. 55), and in combustion experiments using a torch (No. 29, 30). The data on NO_x generation based on fuel weight may be compared with published data on HCN generation from similar materials under similar conditions (18). The quantities of NO_x generated are less than those of HCN, often by a factor of 10. The fuels listed in Table 1 are mostly nitrogen-containing polymers. Some non-nitrogen-containing polymers are also listed (No. 2, 6, 32, 37, 39, 40, 41, 42, 45, 49, 52); clearly, NO_x generation from the burning of such fuels is insignificant.

Mukai (11) burned wool at controlled air/fuel ratios. At 800 C, when the ratio was increased from 0 to 3, the conversion of fuel nitrogen to NH_3 decreased from 35% to 0%, while its conversion to NO increased from 0% to 5%. Mukai considered NH_3 as an intermediate compound in the conversion of fuel nitrogen to NO_x .

In studies of Axworthy et al (19), who pyrolyzed nitrogen-containing fossil fuels and model nitrogen compounds, HCN was considered to be the principal intermediate product in the formation of NO. In the absence of O_2 , the yield of HCN, in terms of the mole ratio to fuel nitrogen, increased with temperature up to 50%. Under Axworthy et al's experimental conditions, i.e., at temperatures higher than 950 C, ammonia was produced in a minor amount. They speculated that in the presence of O_2 , N_2 (and other nitrogen compounds) and NO were formed in competing reactions from the oxidation of HCN. In the studies of Herrington (15) (No. 52-55 in Table 1), who burnt several types of polyurethane foams in a horizontal position in an Ohio State University heat release rate apparatus at 1 W/cm^2 irradiation, relatively high concentrations of NO_x were found. NO_x was always produced in higher concentrations than HCN.

EXPERIMENTAL

Material

A commercially available Acrilan fabric (Type 16, Plain Weave, Test Fabric Inc., NJ, U.S.A.), containing more than 85% polyacrylonitrile (PAN), was used without further treatment. The density of the fabric was 0.20 kg/m^2 .

Pyrolysis/Combustion

Four series of experiments were performed on the burning of the material according to the following schedule:

(a) Horizontal quartz tube. A 0.5 g specimen in a ceramic boat was heated in a 17 mm i.d. quartz tube in an electric oven, and burnt in an air current. The temperature of the oven was isothermally controlled at one of the following levels: 400, 600, 800 or 1000 C.

(b) Oxygen index (20). A 0.7 g specimen was burnt in vertical position in an $\text{O}_2 + \text{N}_2$ current at a supply rate of 300 mL/sec (or 4.7 cm/sec linear velocity). The O_2 percentage was 24, 21 or 18.

(c) Release rate (21). A 72 g specimen was burnt in vertical position under varied air flow rates (15, 30, 60, 120 L/min) and irradiations (1, 2.5, 4 W/cm^2).

(d) Full-scale room (22). In a standard size room (interior dimensions 3.7

x 2.4 x 2.4 m) with a single open doorway, two series of experiments were performed. In a vertical test series, 2 kg of Acrilan fabrics were stapled in two layers to the gypsum wallboard in a corner of the room. The fabric was ignited with a propane sand burner of heat output of 50 kW. In the second series, the same weight of material was burnt in horizontal position; it was placed in two layers on a steel grate (mesh size 2 cm x 4 cm) platform in the centre of the room. The ignition sources were methenamine tablets at five locations.

Analysis of HCN and NO_x

NO_x. The combustion gas was collected in a 15 L polyethylene bag at a pumping rate of 2 L/min for 2.5 min, except in the experiments using the oxygen index tester, where all the exhaust gas from the apparatus was collected during the burning of the sample. In order to oxidize NO to NO₂ (23), sufficient amount of O₂ was added to the bag to raise its concentration to a level higher than 21%. After one hour, 25 mL of deionized water was added. Upon shaking the bag, NO₂ was absorbed in the water to form NO₂⁻ and NO₃⁻. The ions were determined by ion chromatography (IC). The IC apparatus consisted of a Vydac Ion Exchange Column 302IC4.6, Rheodyne 7001 Auto Injector fitted with a 200 L loop, and a Vydac 6000CD conductivity detector. The mobile phase was 4 mmol phthalic acid solution buffered at pH 4.5 with sodium borate. The flow rate was 2 mL/min. The conductivity detector was calibrated with known amounts of NaNO₂ and NaNO₃. The results were spot checked with the colorimetric method of Jacobs and Hochheister (24).

HCN. HCN in the combustion gas was trapped for a period of 30 seconds in a soda lime tube (3 mm i.d., 10 cm long, packed with 20-30 mesh soda lime) as the combustion gas was flowing at a rate of 0.5 L/min. The soda lime was emptied into 50 mL of deionized water. A few drops of 1% lead acetate solution were added to remove the sulfide ions present. Concentrations of CN⁻ were determined by a cyanide electrode method. A series of NaCN solutions of different concentrations were used in the calibration.

RESULTS

The experimental results are presented in Table 2 (a), (b), (c), (d) and Figure 1. In the horizontal tube experiments, which represented the burning condition commonly used by other researchers, the nitrogen in PAN molecules was converted mostly to HCN, especially at higher temperatures, as previously reported (18). The conversion of nitrogen to NO_x occurred to a much lesser degree. The mole ratio NO_x/HCN was 0.1 and 0.02 at 800 C and 1000 C, respectively. In the ASTM heat release rate apparatus experiments the conversion to NO_x was of the same magnitude, on an N-conversion basis, as that observed in the horizontal tube experiments, but the conversion to HCN was much lower. In the full-scale room experiments using propane burners, there was little generation of NO_x. When using methenamine pills, more NO_x and less HCN was formed. The rates of generation of gases are shown in Figure 1.

Toxicity values

According to the Threshold Limits Committee of the American Conference of Governmental Industrial Hygienists, "The chief toxic effect of NO has been ascribed to the formation of methemoglobin and subsequent action on the central nervous system. Animal experiment data indicate that NO is about

one-fifth as toxic as NO₂. The information available on the mechanism of NO intoxication suggests that in mixtures with CO, as well as NO₂, additive effects should be assumed" (25). Montgomery and others determined or estimated the one hour lethal concentration of several toxic gases: CO, 4000 ppm; HCN, 200-300 ppm; NO_x, 200-400 ppm (8). Higgins and others determined the 5 minute LC50 of several toxic gases for rats and mice respectively: NO₂, 831 and 1880 ppm; HCN, 503 and 323 ppm (26). Nishimaru et al determined the LC50 of six toxic gases using mice. The 30 minute LC50 values are: CO, 780 ppm; NO₂, 220 ppm; and HCN, 36 ppm (27). These data indicate that the toxicity of NO_x is comparable to or less than that of HCN.

Table 2(a) Combustion of PAN in a Horizontal Tube

Temp. C	Air flow L/min	Sample g	N-conversion %			NO _x /HCN
			NO _x	HCN	Total	
400	1	0.5	n.d.*	1.2	1.2	-
600	1	0.5	n.d.	2.4	2.4	-
800	1	0.5	0.3	3.3	3.6	0.1
1000	1	0.5	0.15	8.3	8.4	0.02

* not detected

Table 2(b) Combustion of PAN in an ASTM Oxygen Index Test Apparatus

O2 %	Flow L/min	Wt. burned g	Burn time min	Conc. ppm		N-conversion %	
				NO _x	HCN	NO _x	HCN
18	18	0.386	3.17	4		0.16	
21	18	0.861	1.33	27		0.21	
24	18	0.766	1.10	24		0.17	
18	18	0.232	1.42		11		0.35
21	18	0.853	1.48		44		0.38
24	18	0.790	0.83		78		0.41

Table 2(c) Combustion of PAN in an ASTM Release Rate Apparatus

Irradiation W/cm ²	Air flow L/min	Max. conc. ppm		N-conversion %			NO _x /HCN
		NO _x	HCN	NO _x	HCN	Total	
1	15	81	318	0.02	0.05	0.07	0.4
1	30	241	152	0.13	0.02	0.15	6
1	60	177	94	0.14	0.09	0.23	1.5
1	120	35	29	0.05	0.03	0.08	1.7
2.5	60	76	132	0.07	0.06	0.13	1.2
2.5	120	83	42	0.08	0.04	0.12	2.3
4	30	380	870	0.17	0.36	0.53	0.4
4	60	239	780	0.21	0.32	0.53	0.6

Table 2(d) Combustion of PAN in an ASTM Full-scale Room

Ignit. source	Sample orient.	Sample kg	Max. conc. ppm*		N-conversion %			NO _x /HCN
			NO _x	HCN	NO _x	HCN	Total	
Pills	Horizontal	2	33	21	0.53	0.47	1.0	1.3
Pills	Horizontal	2	14	22	0.44	0.34	0.8	1.1
Propane burner	Vertical	2	2	56	0.02	0.68	0.7	0.03
Propane burner	Vertical	2	2	81	0.02	0.65	0.7	0.03

*Concentration in the exhaust duct




Figure 1 Rates of Generation of Gases in a Full-scale Room PAN 2 kg was ignited with pills at horizontal orientation

DISCUSSION

For several materials listed in Table 1 (No. 36, 39-41, 52-55, 56-63), the analytical data were obtained with a chemiluminescent analyzer. Such data require careful examination. According to Felstead et al, HCN, acetonitrile and other nitrogen compounds were converted to NO_2 (76 to 98% for HCN and 102% for acetonitrile) in a chemiluminescent analyzer equipped with a stainless steel high temperature vessel for the conversion of NO_2 to NO (28). HCN was often generated in pyrolysis and combustion in quantities larger than NO_x , as stated earlier in this paper. In the author's studies, acetonitrile was generated in the combustion of PAN (26) and other nitrogen-containing polymers, such as urea-formaldehyde resin, nylons and polyurethane (unreported). Thus the chemiluminescence type NO_x analyzer, when applied to fire gas analysis, may indicate much higher total NO_x concentrations than are actually present.

Earlier studies (18) indicated that in the pyrolysis/combustion of nitrogen-containing fuels the conversion of fuel nitrogen to HCN was sometimes more than 50%. In the present study, the conversion to NO_x was much less than 1%. Again, other data found in the literature suggest that the mole ratio NO_x/HCN is often much smaller than unity. Ratios larger than unity may be attributed to a low conversion to HCN. Such may be the case when the flaming is not too brief, e.g. under 1 or 2.5 W/cm^2 irradiation in the ASTM heat release rate apparatus. Herrington's experiments with polyurethane foams (15) seemed to support this view. Similar results were obtained in experiments conducted in the oxygen index test apparatus and in the full-scale room fire experiments of the present study. At low O_2 percentage in the former experiments and with horizontal position pill ignition in the latter, the HCN concentrations were low. With moderate flaming, there seems to be more chance for HCN oxidation to yield NO_x and other compounds than with brisk flaming such as that occurring at 24% O_2 (Table 2(b)), under 4 W/cm^2 irradiation (Table 2(c)), or in the flame of a hot propane burner (Table 2(d)).




Figure 2 Hypothesis for NO_x and HCN Generation

Based on the experimental data and the hypothesis of Axworthy et al (19), the HCN and NO_x generation may occur as shown in Figure 2. A lower percentage of fuel nitrogen will appear as NO_x from combustion than as HCN from pyrolysis. Since the toxicity of NO_x is comparable to or less than the toxicity of HCN, NO_x is less important than HCN from the point of view of fire gas toxicity.

CONCLUSIONS

According to the literature, less NO_x than HCN (on an N-conversion basis) is generated in the pyrolysis/combustion of nitrogen-containing fuels. In some studies that reported high yields of NO_x , still less NO_x relative to HCN might in fact have been generated since some chemiluminescence type NO_x analyzers may give exaggerated NO_x values in the presence of HCN and acetonitrile. In the author's experiments, conversion of fuel nitrogen to NO_x was, except in one case, much less than 1%. In contrast, conversions to HCN as high as 50% have been reported in the literature. In a moderate flaming combustion, the NO_x /HCN ratio may become larger than unity, because there is more time for HCN oxidation. Since the toxicity of NO_x is comparable to or less than that of HCN, and since less NO_x than HCN is produced, the part played by NO_x in fire gas toxicity is of secondary importance to that of HCN.

ACKNOWLEDGEMENT

The author thanks J. F. Mathieu, D. Lamarche and B. J. Stewart for performing experimental work.

REFERENCES

1. W.D. Woolley, P.J. Fardell, A.B. Atkinson and A.P. Verrall, Conversion of fuels containing nitrogen to oxides of nitrogen in hydrogen and methane flames, *Fire and Materials* 2, 122 (1978).
2. H. A. Watson, H. J. Stark, R. L. Beatty, H. W. Busch and L. B. Berger, Thermal decomposition products and burning characteristics of some synthetic low-density cellular materials, Bureau of Mines Report of Investigations 4777, January 1951.
3. D. Gross, J. J. Loftus, T. G. Lee and V. E. Gray, Smoke and gases produced by burning aircraft interior materials, Report No. NA-68-36, National Bureau of Standards, June 1968.
4. B. Bott, J. G. Firth and T. A. Jones, Evolution of toxic gases from heated plastics, *Br. Polym. J.*, 1, 203 (1969).
5. D. W. Skidmore and P. R. Sewell, The evolution of toxic gases from heated polymers - II, Nitrogen oxides, *Europ. Polym. J.*, 10, 871

(1974).

6. G. W. Armstrong, A chemical/mathematical model for predicting the potential physiological hazard of a changing fire environment, *JFF/Comb. Toxicol.* 1, 157 (1974).
7. L. J. Hillenbrand and J. A. Wray, A full-scale fire program to evaluate new furnishings and textile materials, *JFF/Consumer Prod. Flamm.* 1, 115 (1974).
8. R. R. Montgomery, C. F. Reinhardt and J. B. Terrill, Comments on fire toxicity, *JFF/Combust. Toxicol.* 2, 179 (1975).
9. A. J. Pryor, D. E. Johnson and N. N. Jackson, Hazards of smoke and toxic gases produced in urban fire, *JFF/Comb. Toxicol.* 2, 64 (1975).
10. T. G. Lee, W. J. Parker and M. Trylon, Laboratory fire performance characteristics of a dibromotetrafluoroethane-blown rigid polyurethane foam, *J. Fire and Flamm.* 6, 499 (1975).
11. O. Mukai, Characteristics of pyrolysis and combustion of organic compounds containing nitrogen, *Hitachi Zosen Giho* 38, 232 (1977).
12. R. Hartung, G. L. Ball, E. A. Boettner, R. Rosenbaum and Z. R. Hollingsworth, The performance of rats on a rotarod during exposure to combustion products of rigid polyurethane foams and wood, *J. Comb. Toxicol.* 4, 506 (1977).
13. W. J. Potts and T. S. Lederer, A method for comparative testing of smoke toxicity, *J. Comb. Toxicol.* 4, 114 (1977).
14. J. C. Spurgeon, L. C. Speitel and R. E. Feher, Oxidative pyrolysis of aircraft interior materials, *J. Fire and Flamm.* 8, 349 (1977).
15. R. M. Herrington and B. A. Story, The release rate of heat, smoke and primary toxicants from burning materials, *J. Fire and Flamm.* 9, 284 (1978), and R. M. Herrington, The rate of heat, smoke and toxic gases released from polyurethane foams, *J. Fire and Flamm.* 10, 308 (1979).
16. B. N. Hoschke, J. J. Madden, J. W. Milne and M. F. R. Mulcahy, Toxic gas emission from materials subjected to flame, *J. Comb. Toxicol.* 8, 19 (1981).
17. T. Morikawa and E. Yanai, Evolution of toxicity of effluent gas in a burning room, *Rept. Fire Res. Inst. of Japan*, No. 59, p. 67, March 1985.
18. Y. Tsuchiya, Significance of HCN generation in fire gas toxicity, *J. Comb. Toxicol.* 4, 271 (1977).
19. A. E. Axworthy, V. H. Dayan and G. B. Martin, Reactions of fuel-nitrogen compounds under conditions of inert pyrolysis, *Fuel* 57, 29 (1978).
20. Measuring the minimum oxygen concentration to support candle-like combustion of plastics (oxygen index), *ASTM D2863-77*, Annual Book of ASTM Standards, Part 35, p. 784, American Society for Testing and Materials, 1982.
21. Heat and visible smoke release rates for materials and products, *Annual Book of ASTM Standards*, Vol. 04.07, p. 905, American Society for Testing and Materials, 1984.
22. Room fire experiments, *ASTM E603-77*, Annual Book of ASTM Standards, Vol. 04.07, p. 574, American Society for Testing and Materials, 1984.
23. Japanese Industrial Standards, Methods for determination of oxides of nitrogen in exhaust gases (Explanations), *JIS K 0104-1979* (in Japanese).
24. Jacobs and Hochheister method in Standard methods of chemical analysis, 6th ed., F. J. Welcher ed., p. 634, vol. 2, part A, D. Van Nostrand Co., Princeton, 1963.
25. Documentation of the threshold limit values, 3rd ed., American Conference of Governmental Industrial Hygienists, Cincinnati, Ohio, 1971.
26. E. A. Higgins, V. Fiorica, A. A. Thomas and H. V. Davis, The acute

toxicity of brief exposures to HF, HCl, NO₂ and HCN singly and in combination with CO, FAA-AM-71-41, Nov. 1971, FAA Civil Aeromedical Institute.

27. Y. Nishimaru, Y. Tsuda, T. Sakurai, N. Nagamura, Y. Kuchinomachi, O. Kashida, I. Hieda, M. Yamamura, T. Jin and T. Yamada, Study on evaluation of toxicity by gas using pure gas, Proceedings of the 7th UJNR Panel on Fire Research and Safety, NBS, Washington, October 1983.
28. D. K. Felstead, P. Maddison and D. A. Reilly, Interferences in the determination of nitrogen dioxide in a chemiluminescent analyser, Fire and Materials, 1, 123 (1976).
29. Y. Tsuchiya and K. Sumi, Thermal decomposition products of polyacrylonitrile, J. Applied Polym. Sci., 21, 975 (1977).

This paper is being distributed in reprint form by the Institute for Research in Construction. A list of building practice and research publications available from the Institute may be obtained by writing to the Publications Section, Institute for Research in Construction, National Research Council of Canada, Ottawa, Ontario, K1A 0R6.

Ce document est distribué sous forme de tiré-à-part par l'Institut de recherche en construction. On peut obtenir une liste des publications de l'Institut portant sur les techniques ou les recherches en matière de bâtiment en écrivant à la Section des publications, Institut de recherche en construction, Conseil national de recherches du Canada, Ottawa (Ontario), K1A 0R6.